




2.5/6.0 male to BNC male
A-C42334-A85-A32




2.5/6.0 male to BNC female
A-C42334-A85-A34




2.5/6.0 female to BNC male
A-C42334-A85-A36




2.5/6.0 female to BNC female
A-C42334-A85-A38




2.5/6.0 male to BPO-10 male
A-C42334-A85-A42




2.5/6.0 male to BPO-10 female
A-C42334-A85-A44




2.5/6.0 female to BPO-10 male
A-C42334-A85-A46




2.5/6.0 female to BPO-10 female
A-C42334-A85-A48




2.5/6.0 male to SP male
A-C42334-A85-A52




2.5/6.0 male to SP female
A-C42334-A85-A54




2.5/6.0 female to SP male
A-C42334-A85-A56




2.5/6.0 female to BNC female
A-C42334-A85-A58




BPO-10 male to BPO-10 male
A-C42334-A85-A62




BPO-10 male to BPO-10 female
A-C42334-A85-A64




BPO-10 female to BPO-10 female
A-C42334-A85-A66




BPO-10 male to SP male
A-C42334-A85-A72




BPO-10 male to SP female
A-C42334-A85-A74




BPO-10 female to SP male
A-C42334-A85-A76




BPO-10 female to SP female
A-C42334-A85-A78




BPO-10 male to BNC male
A-C42334-A85-A82




BPO-10 male to BNC female
A-C42334-A85-A84




BPO-10 female to BNC male
A-C42334-A85-A86




BPO-10 female to BNC female
A-C42334-A85-A88




SP male to SP male
A-C42334-A85-A92




SP male to SP female
A-C42334-A85-A94




SP female to SP female
A-C42334-A85-A96




SP male to BNC male
A-C42334-A85-A102



SP male to BNC female
A-C42334-A85-A104



SP female to BNC male
A-C42334-A85-A106



SP female to BNC female
A-C42334-A85-A108


Adaptors

[illegible]

Some Adaptors are only available on extended delivery times.

Special Adaptors available on request on extended delivery times.


Contact our sales offices for current delivery information.




Monitoring non-isolating
A-C42334-A81-A5

Monitoring 1K5 isolating
A-C42334-A81-A10


Monitoring 2K4 isolating
A-C42334-A81-A20



Non-monitoring
A-C42334-A81-A1




Monitoring 1K5 isolating, side entry
A-C42334-A81-A11




Monitoring non-isolating, snap on
A-C42334-A81-A105

Monitoring 1K5 isolating, snap on
A-C42334-A81-A110

Monitoring 2K4 isolating, snap on
A-C42334-A81-A120




Non-monitoring, snap on
A-C42334-A81-A101




Monitoring 1K5 isolating, side entry
A-C42334-A81-A111

Monitoring 1K5 isolating, double side entry
A-C42334-A81-A112




Solid solder – panel mounted
A-C42334-A26-A1




Monitoring non-isolating
A-C42334-A148-A26

Monitoring 2K4 isolating
A-C42334-A148-A30



Non-monitoring
A-C42334-A148-A27




Monitoring non-isolating
A-C42334-A101-A4




Monitoring 2K4 isolating
A-C42334-A101-A6

Monitoring 1K0 isolating
A-C42334-A101-A8




Non-monitoring
A-C42334-A101-A2




Monitoring non-isolating
A-C42334-A91-A20

Monitoring 1K0 isolating
A-C42334-A91-A22


Monitoring 2K4 isolating
A-C42334-A91-A30



Non-monitoring
A-C42334-A91-A10



6-pole audio link
monitoring
A-C42334-A9-A11






6-pole audio link
non-monitoring
A-C42334-A9-A8

U-links

[illegible]

¹⁾ Depends on cable size.

²⁾ Available on request on extended lead times.



To mount 48 of 1.6/5.6 sockets.
Two pack etched and baked enamel on mild steel.
A-C42334-A28-A4

